



FEATURES:

- Model 5113 Mates to Model # 5110 straight cord male plug.
- Model 5129 Mates to Model # 5126 straight cord male plug.
- Wall or Floor mount receptacle.
- Model 5113 will accept standard 3 pin XLR male plugs.
- Model 5129 will accept standard 5 pin XLR male plugs.
- Durable Zinc Alloy housing.
- Accepts up to 14 AWG wire.

MATERIALS:

Housing: Zinc Alloy with a nickel finish

Contacts: Bronze with a Tin finish

Ground Tag: Steel

Insulator: Black Polyester

RATINGS:

Operating Voltage: 133 VRMS/DC.

Current: 15 Amperes.

ORDERING INFORMATION: Models 5113, 5129

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5129 5113/POM