MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-TOGGLE

CATALOG LISTING
112 TW1 SERIES
CHART 2

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CAT. LIST.	RECOMMENDED LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	CIRCUIT WITH TOGGLE IN: EXTREME POSITION KEYWAY SIDE	CENTER	EXTREME POSITION OPPOSITE KEYWAY
112 TW1-1 (3)	A,B,C,D,E,F,G,H,J,K,L,M,N,P	ON	OFF	ON
112 TW1-3 (3)	D, F, G	ON	NONE	ON
112 TW1-5 (3)	E,F,K,L,M,N	MOM ON	OFF	ON
112 TW1-7 (3)	E,L,N	MOM ON	OFF	MOM ON
112 TW1-8 (3)	F	MOM ON	NONE	ON
112 TW1-2 (3)	D,F,G	OFF	NONE	ON

ELECTRICAL DATA

28 VDC & 115 VAC
5 AMP RES
2 AMP IND
1 AMP LAMP



NOTE-
1 - FURNISHED UNASSEMBLED
2 - TERMINATION WILL ACCEPT CRIMP CONTACT CONFORMING TO M39029/1-101
3 SUFFIX MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING
4 MATTE FINISH
5 SWITCH DESIGNED TO CONFORM TO MS 27721 EXCEPT TERMINATION, LENGTH, AND WEIGHT

SCALE 2 TO 1
DO NOT SCALE PRINT
UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT 1.0 OZ MAX

DRAWING NUMBER 112 TW1 SERIES CHART 2 PAGE 1 OF 1
ISSUE 13 M
RELEASE NO. PR-4157
REPLACES
CHECK
RASTER
DRAWN B E N 17 APR 74

REVISIONS

A	PR-4098 112 TW1-3G	B E N 17 APR 74
B	PR-4157	D B W 16 MAY 74
C	CO 50565	T M M 12 DEC 81
D	CO 53417	WJM 27 JUL 83
E	CO 55602	WJM 5 JUL 84
F	CO-95233	J J A 6 JULY 99
G	202167	CSL 17 JAN 01