



KT

Inserts, small



1

Product description

Cable inserts KT small are used with the following cable entry frames:

- KEL(-ER) | Page 6 - 18
- KEL-FG | Page 20 - 21
- KEL-FL | Page 36
- KVT range | Page 22 - 28

The model range KT small is designed for cable diameters from 2 to 17 mm.

Assembly

When installing the insert, the smooth side of the insert faces the middle of the cable entry frame.

Specification KT grey








Material Elastomer
Flame class UL94-Vo, self-extinguishing
Temperature - 40°C to + 90°C (static)
Properties Halogen free, silicone free

Specification KT black

Material Elastomer
Flame class UL94-HB
Temperature - 30°C to + 90°C (static)
Properties Higher chemical resistance, UV-stabilised

Accessories

ST Plugs | Page 35

Description	Type	Order No grey	Order No black	Clamping range	PU
BTK		☐ 41251	☒ 41351	Blind insert	10
		☐ 39934	☒ 41302	2 - 3 mm	10
KT		☐ 41203	☒ 41303	3 - 4 mm	10
		☐ 41204	☒ 41304	4 - 5 mm	10
		☐ 41205	☒ 41305	5 - 6 mm	10
		☐ 41206	☒ 41306	6 - 7 mm	10
		☐ 41207	☒ 41307	7 - 8 mm	10
		☐ 41208	☒ 41308	8 - 9 mm	10
		☐ 41209	☒ 41309	9 - 10 mm	10
		☐ 41210	☒ 41310	10 - 11 mm	10
		☐ 41211	☒ 41311	11 - 12 mm	10
		☐ 41212	☒ 41312	12 - 13 mm	10
		☐ 41213	☒ 41313	13 - 14 mm	10
		☐ 41214	☒ 41314	14 - 15 mm	10
		☐ 41215	☒ 41315	15 - 16 mm	10
		☐ 39901	☒ 39912	16 mm	10
		☐ 39900	☒ 39913	17 mm	10
		☐ 39930	-	approx. 8 × 4 mm	10
KT oval					
KT S1					
KT tele		☐ 39931	-		10
KT tele1		☐ 39929	-	Telephone cable	10
KT tele2		☐ 41257	-	Data cable RJ12	10
		☐ 41258	-	Data cable RJ10 / RJ45	10

*Only valid for grey product types

KT

Inserts, small



Type	Order No grey	Order No black	Clamping range	PU	Description
------	------------------	-------------------	----------------	----	-------------

KT 2 2	☐ 39935	☒ 39936	2× Ø 2 mm	10	 KT 2 x
KT 2 3	☐ 39939	☒ 39940	2× Ø 3 mm	10	
KT 2 4	☐ 39906	☒ 39907	2× Ø 4 mm	10	
KT 2 5	☐ 41200	☒ 39904	2× Ø 5 mm	10	
KT 2 6	☐ 41201	☒ 39905	2× Ø 6 mm	10	
KT 2 7	☐ 41202	☒ 39916	2× Ø 7 mm	10	
KT 2 8	☐ 39917	☒ 39918	2× Ø 8 mm	10	
KT 4 2	☐ 39937	☒ 39938	4× Ø 2 mm	10	 KT 4 x
KT 4 3	☐ 39914	☒ 39915	4× Ø 3 mm	10	
KT 4 4	☐ 39909	☒ 39911	4× Ø 4 mm	10	
KT 4 5	☐ 39908	☒ 39910	4× Ø 5 mm	10	
KT 4 6	☐ 39932	☒ 39933	4× Ø 6 mm	10	
KT-ASI	☐ 39902	☒ 39903	1 ASI-cable	10	 KT ASI2 I
KT-ASI2 I	☐ 39922	☒ 39924	2 ASI-cables	10	
KT-ASI2 II	☐ 39921	☒ 39923	2 ASI-cables	10	
					 KT ASI2 II

*Only valid for grey product types

Product description

Cable inserts KT small are used with the following cable entry frames:

- KEL(-ER) | Page 6 - 18
- KEL-FG | Page 20 - 21
- KEL-FL | Page 36
- KVT range | Page 22 - 28

The model range KT small is designed for cable diameters from 2 to 17 mm.

Assembly

When installing the insert, the smooth side of the insert faces the middle of the cable entry frame.

☐ Specification KT grey

Material	Elastomer
Flame class	UL94-Vo, self-extinguishing
Temperature	- 40°C to+ 90°C (static)
Properties	Halogen free, silicone free

☒ Specification KT black

Material	Elastomer
Flame class	UL94-HB
Temperature	- 30°C to + 90°C (static)
Properties	Higher chemical resistance, UV-stabilised

Accessories

ST Plugs | Page 35