Female Header Micro Match 1,27 mm

Series **369**

pitch **1,27**

termination

max. pincount **026**



Rated current	1,5 A
Rated voltage	230 VRMS / VDC
Withstand voltage	500 VRMS for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

Product group **4**

Variation



1

With locking feature



2



3

With locking feature



4

	no. of contacts	see figure left	see figure left	see figure left	available in variation	
	n	A	B	C		
3	004	7,00	3,81	5,60	1	3
3	006	9,54	6,35	8,14	1	3
3	008	12,08	8,89	10,68	1	3
3	010	14,62	11,43	13,22	1	3
3	012	17,16	13,97	15,76	1	3
3	014	19,70	16,51	18,30	1	3
3	016	22,24	19,05	20,84	1	3
3	018	24,78	21,59	23,38	1	3
3	020	27,32	24,13	25,92	1	3
3	022	29,86	26,67	28,46	1	3
3	024	32,40	29,21	31,00	1	3
3	026	34,94	31,75	33,54	1	3
4	004	9,70	3,81	5,60	2	4
4	006	12,24	6,35	8,14	2	4
4	008	14,78	8,89	10,68	2	4
4	010	17,32	11,43	13,22	2	4
4	012	19,86	13,97	15,76	2	4
4	014	22,40	16,51	18,30	2	4
4	016	24,94	19,05	20,84	2	4
4	018	27,48	21,59	23,38	2	4
4	020	30,02	24,13	25,92	2	4
4	022	32,56	26,67	28,46	2	4
4	024	35,10	29,21	31,00	2	4
4	026	37,64	31,75	33,54	2	4

PCB Layout









Plating:
T = Sn

Packaging:
R = Reel
T = Tube

Variation (1,2,3,4) | No. of contacts | Plating contact | Packaging (R,T)

Order code: 369-?-???-0-NTX-K?0

GARRY

www.mpe-connector.de

CS130212_V2

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany • Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de

Mating series	373	372
see page	3-19	6-5