



## ■ Specification

| Model No.   | Key No.     | Net Weight (g) | Code No. |
|-------------|-------------|----------------|----------|
| THA-302J-1  | Without Key | 584            | 3570     |
| THA-302J-1K | No.2200     | 696            | 4016     |
|             | No.2000     | 696            | 3756     |
| THA-302J-2  | Without Key | 559            | 3571     |
| THA-302J-2K | No.2200     | 587            | 4012     |
|             | No.2000     | 587            | 3732     |
| THA-302J-3  | Without Key | 388            | 3572     |
| THA-302J-3K | No.2200     | 400            | 4017     |
|             | No.2000     | 400            | 3758     |

### ■ Size List

| Model No.     | A   | B  | C  | D     | E    | F  |
|---------------|-----|----|----|-------|------|----|
| THA-302J-1K*1 | 175 | 42 | 23 | 116.5 | 26.5 | 18 |
| THA-302J-2K*2 | 142 | 40 | 23 | 83.5  | 27   | 18 |
| THA-302J-3K*3 | 124 | 34 | 20 | 69    | 26.5 | 15 |

### ■ Size List for Holes

| Model No.     | A1    | B1   | C1  |
|---------------|-------|------|-----|
| THA-302J-1K·1 | 165.5 | 33.5 | 147 |
| THA-302J-2K·2 | 132.5 | 33.5 | 114 |
| THA-302J-3K·3 | 114.5 | 28.5 | 99  |

## ■ Parts List

| No. | Part Name                    | Material  | Finish | Quantity |
|-----|------------------------------|-----------|--------|----------|
| 1   | Body                         | ZDC       | Cr     | 1        |
| 2   | Handle                       |           |        | 1        |
| 3   | Shaft                        |           |        | 1        |
| 4   | Rotor Case                   |           |        | 1        |
| 5   | Packing                      | Elastomer | Black  | 1        |
| 6   | Set Plate                    | SPCC      | Zn     | 1        |
| 7   | Square Hole Washer           |           |        | 1 ※      |
| 8   | Flat Washer                  |           |        | 1        |
| 9   | Cross Hole Head Hexagon Bolt | S         |        | 1        |
| 10  | Rotor                        | SUS/ZDC   | —/Zn   | 1        |
| 11  | Key                          | C3713     | Ni     | 2        |
| 12  | Pan Head Screw               | S         | Zn     | 1~2      |
| 13  | Cam Stopper                  | SPCC      |        | 1        |

※2 pcs of washer is included for No. 7. THA-302J-3K・3.

### ■ Characteristic



Two segment pull out mechanism.  
Protects the fingers from sudden pop out of the handle.

## ■ Application


Distribution boards /  
Distribution panels /  
Control boards /  
Various types of boxes, etc.

## ■ Specification


It can be used for both left and right side by changing the cam 90°. The key No. is all the same. The cylinder is locked at the 180° right turn. The key can be inserted or removed from the locked and unlocked position. Waterproof by its O-ring. 60° turn handle and key No. 200 is available.



The figure shows THA-302-J-2K.  
Note: The shape is slightly different  
for THA-302J-1K an THA-302J-3K.



### ● Instruction



1. By sliding the button downward, the handle shall be popped up slightly.
2. Lift up the handle more.
3. Grip the handle tightly and turn it to open the door.