THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-13-016759	25OCT13	JR	KR



1. TAB DIMENSIONS 0.81±0.025 X 6.35 [.032±.001 X .250]
2. WIRE STRIP LENGTH 7.92 [.312].
3. INSULATION SIZE .320 MAX DIA.
4. SUPPLIED IN LOOSE PIECE.
5. DIMENSION DOES NOT INCLUDE TRIM BURR.
6. 0.38 [.015] MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA.



MATERIAL & FINISH	PART NO
HOUSING: NYLON,COLOR-YELLOW TAB: BRASS,TIN	4-521098-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± 0.38 [.015]
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN	JR RUTH	9/25/95
CHK	P FORTNEY	9/25/95
APVD	D BRATINA	9/25/95
PRODUCT SPEC	108-2017	
APPLICATION SPEC	114-2123	
WEIGHT	-	

CUSTOMER DRAWING

TE Connectivity

NAME: TAB ASSEMBLY, ULTRA-FAST, [6.35] .250 SERIES, 12-10 AWG
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-521098	-

SCALE	SHEET	REV
4:1	1 OF 1	D1