REVISIONS M

TABLE 1		
TERMINAL SPECIFICATION	TERMINAL	"C" REF
−H	T−1R6−X	.300 [7.62]
−R	T−2R6−X	.332 [8.43]
−T	T−3R6−X	.235 [5.97]

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES — TOLERANCES ARE:

ONE PLACE DECIMALS: ± — THREE PLACE DECIMALS: ± — ANGLES ±

TWO PLACE DECIMALS: ± — FOUR PLACE DECIMALS: ±

TITLE: HLT ASSEMBLY

DWG NO: HLT−XXXX−X−X

SHEET 1 OF 1

HLT−XXXX−X−X

ROW SPECIFICATION
(SEE FIG. 1)
EXPRESSED IN NO. OF ROWS
1 THRU 20

BODY LENGTH SPECIFICATION
(SEE FIG. 1)
EXPRESSED IN NO. OF POS. PER ROW
1 THRU 20

PLATING SPECIFICATION
−G: GOLD, SPECIFY −G IN TERMINAL SUFFIX −X
−T: TIN, SPECIFY −T IN TERMINAL SUFFIX −X

TERMINAL SPECIFICATION
(SEE TABLE 1)

PACKAGING TABLE	
ROW SPECIFICATION	PACKAGE IN
−01	PT−1−24−01−23 / TP−12 (2)
−02	PT−1−24−01−14 / TP−03 (2)
−03 & −04	BULK
−05 THRU −20	BEAD BOARD

NOTES:
1.) FILL ALL POSITIONS.
2.) PINS TO ENTER BODY FROM C'BORE SIDE.
3.) BARB ON SOCKET MUST BE VISABLE BELOW BODY.

ASSEMBLY INSTRUCTIONS

DO NOT SCALE FROM THIS PRINT



FIGURE 1

STYLE −H



TERMINALS TO BE RECESSED (COUNTER−SUNK)
INTO BODY TO ALLOW BARB
PROTRUSION AT BOTTOM

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
PET POLYESTER
COLOR: BLACK

TERMINAL:
PHOS BRONZE

MISC\MKTG
HLT−MKT

samtec
520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944−6733 P.O. BOX 1147
CODE 55322

MADE BY: JORDAN 5−29−85
CHECKED BY: THRUSTON 6−4−85
ENGINEER APPROVAL BET 6−4−85

HLT−XXXX−X−X
SHEET 1 OF 1