Capacitor Data Sheet

GRM0337U1H7R4DD01#

"#" indicates a package specification code.

Discontinued | General | 125 ℃max. | Reflow OK | RoHS | REACH

Date of discontinuation: 31 Mar 2014

< List of part numbers with package codes >
GRM0337U1H7R4DD01D , GRM0337U1H7R4DD01W , GRM0337U1H7R4DD01J

Shape



L size	0.6 ±0.03mm
W size	0.3 ±0.03mm
T size	0.3 ±0.03mm
External terminal width e	0.1 to 0.2mm
Distance between external terminals g	0.2mm min.
Size code in inch(mm)	0201 (0603M)

References

Packaging	Specifications	Minimum quantity
D	ϕ180mm Paper taping	15000
J	ϕ330mm Paper taping	50000
W	ϕ180mm Paper taping (W8P1*) * Width : 8mm, Pocket pitch : 1mm	30000

Mass (typ.)	
1 piece	0.33mg
ϕ180mm Reel	118g

Specifications

Capacitance	7.4pF ±0.5pF
Rated voltage	50Vdc
Temperature characteristics (complied standard)	U2J(EIA)
Temperature coefficient	-750±120ppm/℃
Temperature range of temperature characteristics	25 to 85℃
Operating temperature range	-55 to 125℃

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Murata Manufacturing Co., Ltd. URL : http://www.murata.com/

Last updated: 2017/11/23