samtec



(5,08 mm) .200"

HPF SERIES

POWER SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?HPF

Insulator Material:
Black LCP
Contact Material:
BeCu
Plating:
Sn over
50µ" (1,27 µm) Ni
Insertion Depth:
(3,68 mm) .145" to (8,26 mm) .325" (.368" (9,35 mm) plus board thickness minimum for bottom entry)
Wiping Distance:
(0,38 mm) .015"
Insertion Force:
(Single contact only)
56 oz (15,57 N) avg.
Withdrawal Force:
(Single contact only)
52 oz (14,46 N) avg.
Lead–Free Solderable:
Yes
SMT Lead Coplanarity:
(0,15 mm) .006" max (02-10)
(0,20 mm) .008" max (11-20)
RoHS Compliant:
Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594

FILE NO: 016871 0 000

Mates with:
HPM, HPW

POWER EYE CONTACT

HPF/HPM	
PINS	CURRENT RATING (PER CONTACT)
1	16.6 A
2	14.4 A
3	13.2 A
4	12.7 A
ALL	8.9 A



Surface Mount or Through-hole

RUGGEDIZED by SAMTEC

- Three-finger Power Eye contact
- Locking clip option

HPF	–	NO. PINS PER ROW	–	LEAD STYLE	–	PLATING OPTION	–	S	–	OTHER OPTIONS
		02 thru 20		–01 = Through-hole –02 = Surface Mount		–T = Matte Tin				–LC = Locking Clip (Manual placement required) (Style –02 only) –K = (6,50 mm) .256" DIA Polyimide Film Pick & Place Pad –TR = Tape & Reel Packaging (14 positions maximum) (Style –02 only)





Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 **SAMTEC NORTHERN CALIFORNIA** • Tel: +1-408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: +44 01236 739292 **SAMTEC GERMANY** • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 **SAMTEC ITALY** • Tel: +39 039 6890337 **SAMTEC NORDIC/BALTIC** • Tel: +46 8 4477280 **SAMTEC BENELUX** • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 **SAMTEC INDIA** • Tel: +91 80 3272 1612 **SAMTEC ANZ** • Tel: +613 9580 0683 **SAMTEC SINGAPORE** • Tel: +65 6745 5955 **SAMTEC JAPAN** • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 **SAMTEC SHENZHEN** • Tel: +86 755 83776780 **SAMTEC TAIWAN** • Tel: +886 2 2735 6109 **SAMTEC HONG KONG** • Tel: +852 26904858 **SAMTEC KOREA** • Tel: +82 31 717 5685