THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
AJ	16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER EC 0S14–0173–05	26JULY05	BM	JL

1. 100–2, COPPER, H00
2. SILICONE RUBBER PER ZZ–R–765
3. TIN–LEAD PLATE PER ASTM–B–545
4. TIN PLATE PER ASTM–B–545
5. FOR USE WITH: RG–174/U & 188/U CABLE.
6. CRIMPING TOOL: 69245–2.
7. SEE INSTRUCTION SHEET 1799–1
8. SILVER PLATE PER QQ–S–365





RECOMMENDED STRIP LENGTH

	FERRULE	CRIMP END ASSY	PLUG ASSY	PART NUMBER
	4	8	4	9–330058–0
OBSOLETE	8	8	3	7–330058–1
SUPERSEDED BY 2–5330058–1	8	8	3	2–330058–1
	FINISH			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±–
1 PLC ±–
2 PLC ±–
3 PLC ±–
4 PLC ±–
ANGLES ±–

MATERIAL 1 2

FINISH 3 4 8

DWN M.E.	05–24–83	
CHK D. HEIDE	09–13–83	
APVD G.M.	09–13–83	
PRODUCT SPEC —		
APPLICATION SPEC —		
WEIGHT .412 OZ		

tyco Electronics
Tyco Electronics Corporation
Harrisburg, Pa 17105–3608

NAME
CONNECTOR, COAXIAL
RF PLUG, SERIES BNC

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–330058	—

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	1 OF 1	G