Search Results

Evaluate
- Approvals
- PDF FDA Complian
- FAQ's
- Product Bulletins
- PDF Metal Detect..

Design a Solution
- Catalog Cut Sheet
- PDF PLT1M-C86 Pr
- Part Drawings
- PDF Pan-Ty Metal..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PLT3H-L186'**

Your search criteria matched only one product, shown below

PLT3H-L186

- Metal impregnated material allows identification by metal detectors or x -ray inspection to meet food, beverage and pharmaceutical safety standards by helping to reduce product contamination
- One-piece design with locking wedge provides low thread force and reliable installation to improve productivity and reduce operator fatigue
- Distinct blue color per common industry practices provides easy identification on conveyor belts and in finished products, reducing waste due to product contamination
- Excellent chemical resistance for food and pharmaceutical processing equipment manufacturing applications
- For use in processing and packaging areas where aggressive acid and alkaline chemicals are used to clean the equipment
- For indoor use

Part Number	PLT3H-L186
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, 11.1"L (282mm), Metal Detectable Polypropylene, Light-Heavy cross section, Dark Blue
Product Type	Cable Ties
Material	Metal Impregnated Polypropylene
Color	Dark Blue
CSA Certified	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Length (In.)	11.1
Length (mm)	282
Width (In.)	0.300
Width (mm)	7.6
CE Compliant	No
Cross Section	Light-Heavy
Head Height (In.)	0.360
Head Height (mm)	9.1
Head Width (In.)	0.480
Head Width (mm)	12.2
Locking Style	Locking
Material Flammability Rating	HB
Max. Bundle Diameter (In.)	3.00
Max. Bundle Diameter (mm)	76
Max. Continuous Use Temperature	239°F (115°C)
Min. Bundle Diameter (In.)	0.25
Min. Bundle Diameter (mm)	6.4
Min. Loop Tensile Strength (Lbs.)	60
Min. Loop Tensile Strength (N)	267
Plenum-Rated	No
Pricing Description	Cable Tie, 11.1"L (282mm), Light-Heavy, Metal Detectable Polypropylene, Dark Blue
Thickness (In.)	.075
Thickness (mm)	1.9
Tool	GTH, GS4H, GS4EH, STH2, ST3EH
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy