Female Header Right Angled 2,54 mm

Series **095**



Rated current	3,0 A
Rated voltage	250 VRMS / VDC Please consider air- and creepage distances
Withstand voltage	500 VRMS for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch **2,54**

termination

mating pin size **□ 0,64**

max. pincount **040 / 080**

Product group **4**

Variation



1



2

PCB Layout





Plating:
T = Sn
F = Au
S = Selective Au

* No. of contacts:
Variation 1 = 001 - 040
Variation 2 = 002 - 080

Variation (1,2) | No. of contacts * (001,... - 080) | Plating contact (T,F,S)

GARRY

www.mpe-connector.de

CS170611_V2

Order code: 095-?-???-0-N?X-BS0

Mating series	087	089	090	585	088	334	368	296
see page	3-37	3-38	3-39	3-40	3-41	3-42	3-43	3-53

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany • Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de