Search Results

Evaluate
- FAQ's
- Product Bulletins
- PDF Pan-Wrap Spl ..

Design a Solution
- Catalog Cut Sheet
- PDF PW38F-TL Pro
- PDF PW38F-TL Pro
- Part Drawings
- PDF Pan-Wrap Spl ..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PW38F-TL'**

Your search criteria matched only one product, shown below

PW38F-TL

- Slot pattern provides improved flexibility and abrasion protection
- Unique wall design allows easy wire or cable breakouts
- Innovative design maintains uniform bundle protection in dynamic applications; large overlap accommodates a wide range of bundle diameters
- Packaged on a reel for convenient handling and dispensing of product
- Patented installation tool with 180° opening allows easy loading of maximum bundle diameters to speed installation

Notes:
1) Order number of reels required.
2) Diameter can be further reduced with the use of cable ties.
3) Flame retardant products are manufactured from a material that is rated UL 94V -0.

Part Number	PW38F-TL
RoHS Compliancy Status	Compliant
Part Description	3/8" Pan-Wrap™ Split Harness Wrap
Product Type	Pan-Wrap
Material	Polyethylene
Color	Natural
CE Compliant	No
Flammability Rating	HB
Length Per Reel (ft.)	250
Length Per Reel (m)	76.2
Max. Bundle Diameter (In.)	0.43
Max. Bundle Diameter (mm)	10.9
Min. Bundle Diameter (In.)	0.25
Min. Bundle Diameter (mm)	6.4
Nominal Diameter / Size	3/8 inch
Nominal I.D. (In.)	0.38
Nominal I.D. (mm)	9.5
Pricing Description	.375" (9.5mm) Panwrap, Natural, 250 ft. (76m) per roll
Temperature Range	-40°F – 122°F (-40°C – 50°C)
Tool	PWT38
Type	Pan-Wrap
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy