Part Number: 48103-1513

2.50mm Pitch, Wire-to-Board, 15 Circuits, Crimp Housing, Blue

Image not available

Series image - Reference only

Status:	**OBSOLETE**
Replacement:	Contact Molex
Series:	48103
Category:	Crimp Housings

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Mates With Part(s):
48104, 48147

Use With:
48102

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV: Not Relevant
EU RoHS: Compliant
China RoHS:
REACH SVHC: No -ED/39/2015 (15 June 2015)
Low-Halogen Status: Low-Halogen

RoHS Certificate of Compliance (PDF)
Multiple Part Product Compliance Form

Part Detail

COLLAPSE ALL

General

Status	**Obsolete**
Category	Crimp Housings
Series	48103
Application	Signal
Product Name	N/A
UPC	822348527403

Physical

Circuits (maximum)	15
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-25°C to +85°C

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL Database

CSA	LR19980
UL	E29179

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-48103-001
Product Specification	PS-48104-001
Sales Drawing	SD-48103-001
Test Summary	TS-48104-001

Copyright 2015