THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECR-13-004343	30JUL13	KH	KR



1 MATES WITH .032±.001x.250 TAB

2 WIRE STRIP LENGTH .312

3 INSULATION SIZE .320 MAX DIA

4 CONTINUOUS STRIP ON REELS

5 DIMENSION DOES NOT INCLUDE TRIM BURR

6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

MATERIAL & FINISH	PART NO
HOUSING:NYLON,COLOR-BLACK TRANSLUCENT RECEPTACLE: BRASS,TIN	9-520447-2
HOUSING:NYLON,COLOR-YELLOW TRANSLUCENT RECEPTACLE: BRASS,TIN	4-520447-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .015
4 PLC	± -
ANGLES	± -

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN	P FORTNEY	11/4/88
CHK	MS FEHER	11/7/88
APVD	K RANDOLPH	11/7/88
PRODUCT SPEC	108-2043	
APPLICATION SPEC	114-2123	
WEIGHT	-	

TE Connectivity

NAME: RECEPTACLE ASSEMBLY,ULTRA-FAST, .250 SERIES,12-10 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-520447	-

CUSTOMER DRAWING

SCALE	SHEET	REV
4:1	1 OF 1	L