




Dimensions (In.)

Specifications:

- Type: 4mm cermet SMD trimmer
- Resistance tolerance: $\pm 30\%$
- Taper: linear
- Power rating: .2W @ 70°C
- Operating temperature: -30°~+100°C
- Rotational torque: 20~200 gf/cm
- Temperature coefficient: ± 250 ppm/°C
- Working voltage: 100V max.
- Shaft: nickel plated copper
- Wiper: nickel-silver
- Resistive element: RuO₂ Cermet
- Base: ceramic

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[328-43-100K](#) [328-43-50K](#) [328-43-10K](#) [328-43-20K](#) [328-43-500K](#) [328-43-1K](#) [328-43-5K](#)