


**Light bar    10 mm x 20 mm, one segment**

**LG1200**



Notes: All dimensions are in mm (inch)  
Tolerance is  $\pm 0.25$  mm (0.01") unless otherwise specified

**Electro-optical Characteristic: ( $T_a = 25^\circ\text{C}$ )**

Part No.	Chip		Wavelength (nm)	Iv (mcd) @10mA
	Material	Color		Typical
LG1200-RE	GaAsP/GaP	Red	635	12
LG1200-G	GaP	Green	565	10
LG1200-YE	GaAsP/GaP	Yellow	585	10
LG1200-RS	GaAlAs	Red	660	20

**Features**

- Choice of different colors
- Low power consumption
- Easy mounting on PCB and socket
- Wide viewing angle
- Choice of common anode and common cathode

**Description**

LG1200 series are one segment rectangular light bar designed for a variety of applications where a continuous large, bright source of light is required.