Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-Fiber Optic..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F9LD2-2M7'**

Your search criteria matched only one product, shown below

F9LD2-2M7

- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Part Number	F9LD2-2M7
RoHS Compliancy Status	Compliant
Part Description	ST to ST singlemode duplex patch cord, 3mm jacketed cable (two ST connectors on each end) – 9/125?m.
Product Type	ST Patch Cords
Length (m)	7
Fiber Compatibility	9/125?m
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Cable Color	Yellow
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	ST Connector
Connector 2 Type	ST Connector
End Configurations	ST to ST
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	ST-ST LSZH 9µm Dupl 3mm Patch Cord 7m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy