

1/4" 3/8" 1/2"



4549/4550 TORCOFIX K

1-300 N·m / 0.75-220 lbf·ft

Use:

- Controlled screw tightening in the most widely used range of 1 - 300 N·m
- For use in all areas of industrial manufacturing

Features:

- Adjustable torque wrench with a square drive and an integrated ratchet-head function
- For controlled bi-directional tightening
- 1/4", 3/8", 1/2" interchangeable mushroom head-square drive with ball-locking mechanism as per DIN 3120 - A 6.3, A 10 or A 12.5, ISO 1174
- In accordance with DIN EN ISO 6789, traceable to national norms
- Lever-breaking mechanism with a castor guarantee tactile-impulse and audible actuation signals
- Actuation accuracy: +/- 3% tolerance of the scale set torque
- Robust, silk-matt chrome-plated steel tube construction, with chrome-plated ratchet head and glass-fibre-reinforced plastic parts
- Double scale N·m and lbf·ft below a window with a magnifying-glass effect
- Additional micrometer scale with N·m graduation of 0.025; 0.1; 0.25; 0.5 or 1 N·m
- Ergonomically shaped convenient black plastic handgrip
- With an indentation in the middle of the handgrip as a calibration aid

Scope of delivery:

- Test certificate as per DIN EN ISO 6789
- Operating instructions
- The individual wrench is delivered in a transparent plastic box with a practical suspension mounting.

Code	No.	Drive	N·m	lbf·ft	mm	mm	mm	mm	mm
1545124	4549-01	1/4"	1-5	0,75-3,7	220	35	18	0,025 N·m	300
1545132	4549-02	3/8"	2-25	1,5-18	285	35	18	0,1 N·m	450
1545140	4549-05	1/2"	5-50	4-37	335	35	18	0,25 N·m	540
7601530	4550-10	1/2"	10-100	8-75	395	44	22	0,5 N·m	900
7601610	4550-20	1/2"	20-200	15-150	485	44	22	1 N·m	1100
7601880	4550-30	1/2"	60-300	45-220	575	44	22	1 N·m	1400