ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 880					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	B	Revised and Redrawn		1/11/93				
1210	C	Renamed-was 861-*	JWM	7/28/01	JC	8/9/01	JC	8/9/01



MOUNTING HOLE LAYOUT

PART NUMBER	COLOR
861-B	BLACK
861-BL	BLUE
861-GR	GREEN
861-OR	ORANGE
861-R	RED
861-V	VIOLET
861-W	WHITE
861-Y	YELLOW

1. MATERIAL:
   CONTACT: PHOSPHOR BRONZE
   PER QQ-B-750
   BODY: NYLON 66 PER ASTM D4066
2. CONTACT FINISH: BRIGHT TIN
3. HARDWARE: NICKEL PLATED NUT
4. PANEL THICKNESS: UP TO .343" [8.8mm]
5. BODY THREAD STRIPPING TORQUE:
   6.0 LB. IN. [7 KG. CM.]
6. FLAMMABILITY: UL94V-2
   SELF-EXTINGUISHING
7. CONTINUOUS USE TEMPERATURE:
   -40°F (-40°C) TO 185°F (85°C)
8. CURRENT RATING: 15 AMPS
9. BREAKDOWN VOLTAGE: 7000 VRMS MINIMUM
10. CONTACT RESISTANCE: .010 OHMS MAX.
11. CONTACT-TO-PANEL CAP.: 2.4 pF NOMINAL
12. FOR STANDARD .175" TIP PLUGS.
13. KEYED MOUNTING WITH DOUBLE FLATS
14. ACCEPTS UP TO 16 GAUGE WIRE
15. WEIGHT: .0058 lbs

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Tolerances Unless Otherwise Specified:
.X=±.015
.XX=±.010
.XXX=±.005

DRAWN BY:	DATE:
JP	1/11/93
CHECKED BY:	DATE:
JOHN COLE	1/14/93
APPROVED BY:	DATE:
J.Liska	1/19/93

SPC TECHNOLOGY

DRAWING TITLE: Tip Jacks (Standard)

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-376	TA-376.dwg	C

SCALE: NTS | U.O.M.: INCHES [mm] | SHEET: 1 OF 1

SPC-F005.DWG