


Pin Header Shrouded 2,54 mm

Series

093



Rated current	3,0 A
Rated voltage	150 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds


All dimensions in mm.

pitch	2,54
termination	
contact size	
max. pincount	064



Product group
3

Variation



PCB Layout




1



2



3



Plating:	Packaging:	Cap:
T = Sn	S = Standard	0 = Without cap
F = Au	R = Reel	1 = With cap
S = Selective Au		

Variation (1,2,3)

No. of contacts

Plating contact (T,F,S)

Packaging (S,R)

Cap (0,1)



Order code:

093 - 2 - 2 - 2 - 0 - 2 - B 2 2

Mating series	101	430
see page	6-9	6-10