

NOTES:

MATERIAL
1.Insulator Material:PBT+30%GF(UL94V-0),Black
2.Contact Material : Phosphor Bronze
3.Contact Plating : Gold flash/ Tin Over Ni

ELECTRICAL
1.Current Rating : 1AMP
2.Withstand Voltage : 500V AC/DC
3.Contact Resistance : 20mΩ max
4.Insulation Resistance: 1000MΩ min

ENVIRONMENTAL
1.Operation Temperature: -40°C to +105°C
2.Packing: Tray

No. of contacts: 06, 08,10,12,14,16,18,20,22,24,26
30,34,36,40,44,50,60,64 ,68

⑦ Wire Spec: AWG28

RoHS compliant
unit:mm

Scale	Free
TOLERANCE	
X.	±0.35
.X	±0.25
.XX	±0.20
.XXX	±0.15
DIM	TOL
Angle	TOL

Id.	modification	Date	Name
⑧	Update Description	15.03.2022	Winnie
⑦	Add wire spec	27.09.2016	Jesse
⑥	Add the UL-File No	13.12.2013	Winnie
⑤	Delete page 2	22.11.2013	Ray
④	Added 68 Pin	24.12.2009	Dean
③	Correct P/N	28.10.2009	Dean

	Name	Date
Drawn	Alex	25.01.2006
Approved	Jesse	27.09.2016

ASSMANN WSW components

Description: ⑧ DIN 41651 / IDC-socket
2.00mm pitch
with central polarisation

ASSMANN WSW-NO.
AWP2 xx-7240 ②

Drawing-No.
ASS 2309 CO

rev08

Customer-No.

SHEET
1 / 1