Alle Rechte vorbehalten/ *All rights reserved*



Wire	Cu tinned
Gauge	AWG 28/7
Voltage rating	300 Vr.m.s
Current (Max)	2,1A at 25°C
Conductor resistance	221 mΩ/m
Capacity unbalanced	42,7 pF/m
Impedance unbalanced	105 Ω
Inductance unbalanced	0,68 µH/m
Signal delay	4,9 ns/m
Insulation material	PVC
Temperature rating	-20°C (operating) / -30°C (static) to 105°C
Flammability rating	UL: VW1
Insulation resistance	100 MΩ/km
Approval	UL AWM style 2651

Colour code sequence (in 10 steps):

- brown
- red
- orange
- yellow
- green
- blue
- violet
- grey
- white
- black

				Dat.	Name
			Detail.	14/05/07	PK
			Insp.		
			Stand.		
EC01446	22/02/10	SC			
33990	14/05/07	PK			
Mod.	Dat.	Name			

All Dim. in mm
Orig. Size DIN A 4

SEK 18 rainbow Flat cable
9 poles, length per reel: 30,48 m
IEC 918

Maßstab/ *Scale* 10:1

HARTING EURL
F-95972 Paris

TB 09 18 009 7005

Sub.

Blatt/ *Page* 1/1