OGA DIAGONAL: 19.77 [502.25]
VA DIAGONAL: 19.06 [484.14]
PA DIAGONAL: 17.97 [456.45]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8411-203	98-0003-2587-2	FFC	4.27" [108.46]	AG500	23655
17-8411-221	98-0003-2189-7	SER	4.27" [108.46]	AG500	23655
17-8411-206	98-0003-2588-0	NOV	SEE DWG	AG500	23655
17-8411-218	98-0003-2951-0	USB R	4.27" [108.46]	AG500	23655



PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 941±10%
2. NICOMATIC HOUSING P/N: OLO5
   NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
   HOUSING ORIENTED WITH LATCH DOWN

REV	CHANGE NOTICE	DATE	DRW
J	REVISED PER CO 036256	4/13	SB
H	REVISED PER CO 033533	9/11	SB
G	REVISED PER CO 033455	8/11	SB

UNITS: INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED
.X ±
.XX ±.03 [.76]
.XXX ±.015 [.38]
ANGLES ±1°
THIRD ANGLE PROJECTION
DO NOT SCALE DRAWING
SCALE 1 = 1

3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN K CROWLEY 9/05

TITLE
MARKETING DRAWING
SCT32NN 19.06"

CAD FORMAT AUTOCAD
SHEET 1 OF 1
SIZE C
DOCUMENT NO. 28257-MKT
REV J