US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
98-0003-3189-6	FFC	6.00" [152.40]	AG500	23655
98-0003-3190-4	USB R	6.00" [152.40]	AG500	23655

OGA DIAGONAL: 16.43 [417.43]
VA DIAGONAL: 15.75 [400.02]
PA DIAGONAL: 14.86 [377.32]



PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 602±10%
2. NICOMATIC HOUSING P/N: OLO5
   NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
   HOUSING ORIENTED WITH LATCH DOWN

REV	CHANGE NOTICE	DATE	DRW
E	REVISED PER CO 034264	2/12	SB
04	REVISED PER CO 031197	12/09	SB
03	REVISED PER CO 030463	6/09	SB

UNITS: INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED
.X ±
.XX ±.03 [.76]
.XXX ±.015 [.38]
ANGLES ±1°

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

SCALE 1 = 1

3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

DRAWN AH 12/08

TITLE
MARKETING DRAWING
SCT32NN 15.75" W

CAD FORMAT AUTOCAD
SHEET 1 OF 1

SIZE C
DOCUMENT NO. 36386-MKT
REV E