Search Results

Evaluate
- FAQ's
- Product Bulletins
- PDF-Fully Automa..
- Videos
- WMV-Robotic Kit..
- WMV-Automatic Ca..

Design a Solution
- Catalog Cut Sheet
- PDF-ATM-W187-M P
- Part Drawings
- PDF-Auto Tie Mou

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'ATM-W187-M30'**

Your search criteria matched only one product, shown below

ATM-W187-M30

- Multiple sizes work with industry standard panel thickness and hole diameters for greater application flexibility
- Low profile design keeps bundle close to mounting surface, saving space and providing greater protection for bundles in high vibration applications
- Supports compatible cable ties

Part Number	ATM-W187-M30
RoHS Compliancy Status	Compliant
Part Description	Cable Tie Mount, Auto, Winged, .187"(4.75mm) Hole, Black, H.S.Nylon
Product Type	Cable Tie Mounts- Through Panel Hole
Material	Heat Stabilized Nylon 6.6
Color	Black
Height (In.)	0.58
Height (mm)	14.6
Length (In.)	0.80
Length (mm)	20.5
Width (In.)	0.35
Width (mm)	9.0
CE Compliant	No
Environment	Indoor/High Temp
Max. Panel Thickness (In.)	0.12
Max. Panel Thickness (mm)	3.0
Panel Hole Diameter Range (In.)	0.17 – 0.20
Panel Hole Diameter Range (mm)	4.3 – 4.9
Pricing Description	Cable Tie Mount, Auto, Winged, .187"(4.75mm) Hole, Black, H.S.Nylon
Sub Brand	Cable Tie Mount
Type	Through Hole
Used With Cable Ties	BT1.5M-XMR, PLT1.5M-XMR
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy