Search Results

Evaluate
- FAQ's

Design a Solution
- Part Drawings
- STP-Winged Push..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'PWMS-H25-M120'**

Your search criteria matched only one product, shown below

PWMS-H25-M120

Mounts are inserted into pre -drilled holes. The winged base applies pressure on the panel wall to provide a more secure mount in high vibration applications.

• Requires no adhesive or additional mounting hardware
• Can be used where only one side of the panel is accessible
‡Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number	PWMS-H25-M120
RoHS Compliancy Status	Compliant
Part Description	Winged Push Barb Cable Tie Mount
Product Type	Cable Tie Mounts- Through Panel Hole
Material	Weather Resistant Nylon 12
Color	Black
UL Recognized	E136577
Height (In.)	0.61
Height (mm)	15.5
Length (In.)	0.75
Length (mm)	19.1
Width (In.)	0.37
Width (mm)	9.4
Environment	Outdoor
Flammability Rating	UL 94-HB
Max. Panel Thickness (In.)	0.11
Max. Panel Thickness (mm)	2.7
Mounting Method	Push Barb
Panel Hole Diameter (In.)	0.250
Panel Hole Diameter (mm)	6.5
Pricing Description	Cable Tie Mount, Winged Push Mount, WR Nylon 12, BL
Sub Brand	Cable Tie Mount
Temperature Range	-60°C – 85°C
Thickness (In.)	0.23
Thickness (mm)	5.8
Type	Through Hole
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy