REV.	DATE	DESCRIPTION
NC	07/29/02	INITIAL RELEASE



8			
7			
6	FERRULE	COPPER	NICKEL
5	SLEEVE	DELRIN	NATURAL
4	CONTACT PIN	PHOS. BRONZE	GOLD
3	BARREL	BRASS	NICKEL
2	INSULATOR	TEFLON	NATURAL
1	BODY/HOUSING	BRASS	NICKEL
	DESCRIPTION	MATERIAL	FINISH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS

DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERANCE ONLY

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:

.XXX = ± 0.005"
.XX = ± 0.010"
.X = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	07/29/02
CHECKED		
ISSUED		

Amphenol - Connex
CONNECTOR CORPORATION

TITLE
BNC PANEL JACK – W/ #3-56 TAPPED HOLES
(FOR RG-174/U, 188A/U, 316/U CABLE)

SIZE	FSCM NO.	DWG. NO.	REV.
A	99001	112288-11.DWG	NC
SCALE NA	PART NO. 112288-11		SHEET 1 OF 1