




Cat. 5e RJ45 Plug (Industrial IP67, Plastic, Metallized Plastic or Die Cast version with Bayonet Locking Type)

Cat. 5e RJ45 Plug (Industrial IP67, Plastic, Metallized Plastic or Die Cast version with Bayonet Locking Type)

Cable Length*	Part Number							
	Plastic Version				Metallized Plastic Version		Die Cast Version	
L	Cat. 5e UTP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor UTP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable
0.55 ± 0.01 m	--	--	--	--	--	17-501194	--	--
1 ± 0.03 m	17-131074	17-131084	17-131094	17-131104	17-131114	17-131124	17-131134	17-131144
1.2 ± 0.03 m	17-131154	--	--	--	17-131164	--	--	--
1.5 ± 0.03 m	--	--	--	--	--	17-501174	--	--
2 ± 0.05 m	17-10003	17-101144	17-103104	17-103134	17-10025	17-101174	17-100514	17-101204
3 ± 0.05 m	17-130204	17-130214	17-130224	17-130234	17-130244	17-130254	17-130264	17-130274
4 ± 0.05 m	17-10004	17-101154	17-103114	17-103144	17-10026	17-101184	17-100524	17-101214
5 ± 0.1 m	17-10005	17-101164	17-103124	17-103154	17-10027	17-101194	17-100534	17-101224
7.5 ± 0.1 m	--	17-132444	--	--	--	--	--	--
10 ± 0.1 m	17-130284	17-130294	17-130304	17-130314	17-130324	17-130334	17-130344	17-130354
15 ± 0.1 m	17-132704	17-132454	17-132574	17-132584	17-132594	17-132604	17-132614	17-132624
20 ± 0.2 m	17-132634	17-132644	17-132654	17-132664	17-132674	17-132464	17-132684	17-132694
25 ± 0.3 m	17-131174	17-131184	17-131194	17-131204	17-131214	17-131224	17-131234	17-131244

Notes:

- Electrical:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Connector Operating Temperature: -40°C to +85°C
- Materials and Finish:
 - Coupling Ring: Polyester (Black), Metallized ABS or Die-cast (Nickel Plated); UL94 V-0
 - Plug Housing: Polyester (Black) or Metallized ABS (Nickel Plated); UL94 V-0
 - Interfacial Seal: Silicon, Color: White
 - Cable Gland: PA (Black) or Brass, Nickel Plated
 - Cable Gland Seal: NBR, Color: Black
 - Cable Gland Insert (Metal Version): Nylon, Color: White
 - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
 - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
 - Cable: See Part Number table

RoHS Compliant

Customer:				Tolerance		Autodesk Inventor	Scale: 1.8:1	Dim. in
				Unless otherwise specified				
Name				Dimensional:		Angles	Material: See Notes	RJ45 Cat. 5e Ethernet Patch Cords Industrial to Industrial
Title				Angles				
Approval Date				Date		Name		Drawing No.: 39K1A298
n 1 x n Dec/05/2017 Vincent ke				2006		Vincent Ke		
m 1 x m Dec/12/2016 Vincent Ke				Draw. Mar. 05		J. Chaudry		Part No.: SEE P/N ABOVE
L 1 x L Nov/10/2016 Vincent Ke				Appd. Mar. 05		D-old		
k 1 x k Nov/10/2016 Vincent ke				Norm				Sheet 1/1
j 1 x j Mar/27/2014 Vincent Ke				D-old				
i 1 x i Feb/27/2014 Vincent ke								
a original								
Rev. Changes				Date		Name		

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-10003](#) [17-10004](#) [17-10005](#) [17-10025](#) [17-10026](#) [17-10027](#) [17-100514](#) [17-100524](#) [17-100534](#)