








SPECIFICATION
MATERIALS:
HOUSING & INSERT: PBT YELLOW
COUPLING: BRASS-NICKEL PLATED
O-RING: VITON
ELECTRICAL:
VOLTAGE: 10-30VDC
CURRENT RATING: 4A PER PORT, 12 AMPS MAX.
PROTECTION CLASS: IP68
OPERATING TEMPERATURE: -25°C to +90°C

NOTES:
FIXING HOLES TO SUIT M4 SCREWS

| MATERIAL NUMBER | OLD PART NUMBER | FINISHED LENGTH | CABLE JACKET MATERIAL |
|---|---|---|---|
| 1201148027 | BKY8050-FBP-10 | 10M ± 50MM | PUR 3x0.75+16x0.34 |

DESCRIPTION
EC NO: WEU2010-0450
DRWN: REISSNER 2010/03/22
CH'KD: FP ----
APPR: NSTAUDIG 2010/03/23
DESCRIPTION
1
REV

QUALITY SYMBOLS
▼ = 0
Ⓒ = 0

| GENERAL TOLERANCES (UNLESS SPECIFIED) | mm | INCH |
|---|---|---|
| 4 PLACES | ±--- | ±--- |
| 3 PLACES | ±--- | ±--- |
| 2 PLACES | ±--- | ±--- |
| 1 PLACE | ±0.3 | ±--- |
| ANGULAR ± --- ° | | |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM ONLY
SCALE: 1:1
DESIGN UNITS: METRIC
THIRD ANGLE PROJECTION

DRAWN BY: REISSNER DATE: 2010/03/22
CHECKED BY: NS DATE: 2010/03/22
APPROVED BY: NSTAUDIG DATE: 2010/03/23

MICRO-CHANGE MPIS
8 PORT TOP MOUNT
CABLE PUR

molex MOLEX INCORPORATED

MATERIAL NO.: SEE TABLE
DOCUMENT NO.: SD-120114-079
SHEET NO.: 1 OF 1
SIZE: A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION