Knowledge Base

- Clippard's Automated Pneumatic Stamping Machine
- Clippard Controls Breathe Life into Astroworld Hippos
- Pneumatic Solutions for Oxygen Concentration
- Modular Circuit Assembly Tips
- Pneumatic Solutions for Leak Testing
- Clippard Value-Added Services

more...



URH1-0804-BRS-050

Inner Diameter
1/8"

Color
Solid Brown

Length
50 feet

(In Stock)

Qty: 1 Add to Cart

Details

Polyurethane Hose, 1/4" OD-1/8" ID, Solid Brown, 50' Roll

Notes

In normal application hose clamps are not required with hose when used with Clippard hose barb fittings

See Catalog: Page 331

Additional Information

Bend Radius	3/8"
Color	Solid Brown
Inner Diameter	1/8"
Length	50 feet
Static Burst Pressure	Approx. 425 psig at 70°F
Working Range	0 to 105 psig at 100°F Maximum 120°F