REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED

NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: 9205-HS
   INSULATOR: HEAT SHRINK TUBING 221. BLACK.
   BODY: BRASS. 40µ [1.02µm] MIN GOLD OVER NICKEL PLATED.
   CONTACT: BeCu OR PHOSPHOR BRONZE. 40µ [1.02µm] MIN GOLD OVER NICKEL PLATED.

2. P/N: 9203COLOR
   HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
   FRAME: BRASS. NICKEL PLATED.
   CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

3. P/N: W-200/COLOR
   22AWG 65X40 TINNED COPPER
   0.070 [1.78] O.D. PVC INSULATION
   AVAILABLE IN TEN COLORS.

4. PERFORMANCE
   MAXIMUM CURRENT: 2.5 AMPS
   MAXIMUM VOLTAGE: 1000 (300 UL) W.V.D.C.
   MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS ± DECIMALS .XX ± .XXX ± ANGLES ±	CONTRACT NO.	E-Z-HOOK® DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.
			APPROVALS / DATE	
			DRAWN R.L. 10/10	DESCRIPTION 0.025 [0.64] SQ. SKT TO STK STD BAN PLUG (9203)
		MATERIAL SEE NOTE.	APPROVED BY	
		FINISH SEE NOTE.		SIZE A / CODE IDENT NO. 08505 / DRAWING NO. 9169 / REV.
NEXT ASSY	USED ON			
APPLICATION		DO NOT SCALE DRAWING		SCALE 1:1 / SHEET 1 OF 1

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-Z-HOOK. THE INFORMATION IS NOT TO BE REPRODUCED WITHOUT PRIOR WRITTEN PERMISSION OF E-Z-HOOK, DIV. OF TEKTEST INC.
MAXIMUM TESTED RATINGS IN A HANDS-FREE CONTROLLED ENVIRONMENT. MAXIMUM RATINGS ARE NOT TO BE USED CONCURRENTLY.