




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	10A 14V DC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		
Switch Function	SEE CHART		

Frames are nylon (UL flame: 94V-2).
Actuators are Black, PC (94V-2).
Illuminated Actuators are molded in PC, available in Red, Amber or Green Colors.
Waterproof Rubber: Black, Silicone.
Terminals are silver plated brass.
Waterproof and Dustproof to fit IP-65.



FUNCTION		TERMINAL
A 2 OFF (ON) 2P SPST	B 2 OFF ON 2P SPST	0 1 .250" SQ
A 2 L OFF (ON) 3P SPST (LED)	B 2 L OFF ON 3P SPST (LED)	

() = Momentary Function

RoHS Compliant

CW INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 1/28/11	Rev. 0	Unit: mm	Checked By: G.Guld
	Title: PUSH BUTTON SWITCH		CW P/N: GPB553X2SERIES	