

DIN Connector, Plug, 7-pole, solder terminal



7-pole



#### Description

- Solder terminal:
- for cable mounting
- DIN Plug: 7-pole, straight

#### Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

#### Technical Data



Diameter	9.0 mm
Number of Poles	7-pole
Ratings DC	2A / 12VDC
Ratings AC	1A / 100VAC
Dielectric Strength	250VAC
Insulation Resistance	> 50 MΩ @ 250VDC

Allowable Operation Temp.	-20°C to 70°C
Terminal	solder terminal silver plated
Lifetime	5000 Insertions

#### Dimensions



Cable diameter max. 5.0 mm



#### All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
DIN Plug/Socket	9.0	7-pole	solder terminal	4850.1710

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

## Mating Outlets/Connectors



## Category / Description

DIN Plug/Socket Overview complete

4850, 7-pole, Socket, PCB terminals, DIN Plug/Socket 4850.2710

4850, 7-pole, Line Socket, solder terminal, DIN Plug/Socket 4850.3700

DIN Plug/Socket further types to 4850 DIN-Stecker, verschiedene

05.10.2014