


# C-230-S Slide



| Catalog Number | A     | B (min) | B (max) | C     | D     | E (min) | E (max) | F | G    | Load Capacity |
|----------------|-------|---------|---------|-------|-------|---------|---------|---|------|---------------|
| C-230-S-112    | 12.00 | 15.00   | 15.00   | 11.00 | 8.25  | 2.25    | 2.25    | 3 | 1.81 | 140 LBS.      |
| C-230-S-114    | 14.00 | 18.00   | 18.00   | 13.00 | 12.13 | 0.38    | 0.38    | 4 | 1.81 | 140 LBS.      |
| C-230-S-116    | 16.00 | 16.00   | 18.00   | 13.00 | 12.13 | 0.38    | 2.38    | 4 | 3.81 | 135 LBS.      |
| C-230-S-118    | 18.00 | 22.00   | 22.00   | 17.00 | 12.13 | 4.38    | 4.38    | 4 | 3.81 | 135 LBS.      |
| C-230-S-120    | 20.00 | 20.00   | 22.00   | 17.00 | 16.00 | 0.50    | 2.50    | 5 | 5.81 | 130 LBS.      |
| C-230-S-122    | 22.00 | 26.00   | 26.00   | 21.00 | 16.00 | 4.50    | 4.50    | 5 | 5.81 | 130 LBS.      |
| C-230-S-124    | 24.00 | 24.00   | 26.00   | 21.00 | 16.00 | 4.50    | 6.50    | 5 | 7.81 | 125 LBS.      |

## TO ORDER, SPECIFY

**C-230-S** -  -  -

Stationary Section  
1 - Cabinet Mount  
2 - Strap Mount  
4 - Closed Slot


Length

AR - Automatic Release if desired

For information on Strap Mount option see page 27.


## Notes

- Right hand and left hand slides are identical. Set contains 2 right hand slides.
- Finish: All standard slides are coated with Poxylube™ dry film lubricant.
- All standard slides are designed to lock-out in the extended position and are available with an optional automatic release if lock-out is not desirable.
- Standard hardware packages include all the hardware necessary to mount your Chassis Trak® slides:
  - Rear mounting bracket (B-131) included
  - Bar Nuts (CA8056-06-0020)
  - #10-32 screws and keps nuts
- All sliding members of the standard slide are made from cold rolled steel.
- All Chassis Trak® solid bearing slides are supplied with a quick disconnect feature.
- Optional mounting patterns, slide lengths and extensions are available.
- For optional mounting brackets see page 35.



# Strap Mounting Option

## C-230 Strap Mount




| A     | B     |
|-------|-------|
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |

### Notes

1. To order, specify **C-230-S-2XX** see pages 14-15 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.

## C-300 Strap Mount




| A     | B     |
|-------|-------|
| 10.00 | 8.50  |
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |
| 26.00 | 24.50 |
| 28.00 | 26.50 |
| 30.00 | 28.50 |

### Notes

1. To order, specify **C-300-S-2XX** see pages 16-17 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.

## CTS Strap Mount



| A     | B     |
|-------|-------|
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |

### Notes

1. To order, specify **CTS-2XX** see pages 18-19 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.


# Optional Mounting Brackets





**Matrix For Solid Bearing Slides & Appropriate Rear Mounting Brackets with Range of Extension**

|         | B-131*   | B-131-2     | B-131-2.5   | B-131-3      | B-131-3.5    | B-131-4      | B-307-1<br>B-814-1 | B-307-2<br>B-814-2 | B-810-1   | B-810-2   |
|---------|----------|-------------|-------------|--------------|--------------|--------------|--------------------|--------------------|-----------|-----------|
| C-230-D | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| C-230-S | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTD     | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTS     | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTRD    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTRS    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTHD    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHS    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHRD   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHRS   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| C-857   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    |           |           |

Note brackets are made from 16 gauge C.R.S. — Standard finish: clear zinc commercial plating

\*Supplied with standard slides

| CATALOG NUMBER | A    |                                                                                     |
|----------------|------|-------------------------------------------------------------------------------------|
| B-131          | 1.56 |  |
| B-131-2        | 2.00 |                                                                                     |
| B-131-2.5      | 2.50 |                                                                                     |
| B-131-3        | 3.00 |                                                                                     |
| B-131-3.5      | 3.50 |                                                                                     |
| B-131-4        | 4.00 |                                                                                     |

|                                                                                                                                                                |  |  |    |   |                             |      |      |    |                             |      |      |    |  |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----|---|-----------------------------|------|------|----|-----------------------------|------|------|----|--|--|
|                                                                                                                                                                                                                                                   | <b>B-307</b>                                                                         | <b>B-810</b>                                                                          |    |   |                             |      |      |    |                             |      |      |    |  |  |
|                                                                                                                                                                                                                                                   |  |                                                                                       |    |   |                             |      |      |    |                             |      |      |    |  |  |
|                                                                                                                                                                                                                                                   | <b>B-814</b>                                                                         |                                                                                       |    |   |                             |      |      |    |                             |      |      |    |  |  |
| <table><tr><th>CATALOG NUMBER</th><th>A</th><th>B</th><th>C</th></tr><tr><td>B-307-1 / B-810-1 / B-814-1</td><td>5.94</td><td>4.38</td><td>16</td></tr><tr><td>B-307-2 / B-810-2 / B-814-2</td><td>9.69</td><td>8.13</td><td>28</td></tr></table> | CATALOG NUMBER                                                                       | A                                                                                     | B  | C | B-307-1 / B-810-1 / B-814-1 | 5.94 | 4.38 | 16 | B-307-2 / B-810-2 / B-814-2 | 9.69 | 8.13 | 28 |  |  |
| CATALOG NUMBER                                                                                                                                                                                                                                    | A                                                                                    | B                                                                                     | C  |   |                             |      |      |    |                             |      |      |    |  |  |
| B-307-1 / B-810-1 / B-814-1                                                                                                                                                                                                                       | 5.94                                                                                 | 4.38                                                                                  | 16 |   |                             |      |      |    |                             |      |      |    |  |  |
| B-307-2 / B-810-2 / B-814-2                                                                                                                                                                                                                       | 9.69                                                                                 | 8.13                                                                                  | 28 |   |                             |      |      |    |                             |      |      |    |  |  |