









Note:

Material:

1.1 Insulator: High Temperature Thermoplastic with g.f UL94V-0
1.2 Contact: Phosphor Bronze, T=0.25mm
1.3 Shell: Spcc, T=0.40mm

2.Specification:

2.1 Current Rating: 1 A Max
2.2 Dielectric Withstanding: Voltage: 750 V(ac) for 1 min
2.3 Contact Resistance: 30 m Max
2.4 Insulation Resistance: 1000 m Min
2.5 Total Mating Force: 3.0 Kgf Max.
2.6 Total Unmating Force:0.5 Kgf Min
2.7 Temperature Range: -55°C~ 85°C

1.Series No.
2.Type: Z=MINI USB
3.Contact Number: 05
4. Contact Type: F=Female
5.Contact Area Plating: C=15u" Gold(Selective)
6.Type: B=BType
7.DWG. No.

RoHS Complaint

Scale	1:1							Name
TOLERANCE								
X.X	±0.40					Drawn	10.19.11	Chappell
X.XX	±0.25					Approved		
X.XXX	±0.15							
Angle	±3°							
			Modification	Date	Name			

ASSMANN WSW components

Item No.
A-USBB-M5-TOP-R (Version 1.1, 5µ")
A-USBB/2-M5-TOP-R (Version 2.0, 30µ")

Title
USB, Version B-Mini, 5-Poles, Top Entry, Black

Drawing No.

rev00

Replace

Sheet