




FEMALE PLUG WITH SNAP-IN MOUNTING FOOT PIN SPACING 3.81 MM / 0.15 IN 100% PROTECTED AGAINST MISMATING



**FEMALE PLUG WITH SNAP-IN
MOUNTING FOOT PIN SPACING 3.81
MM / 0.15 IN 100% PROTECTED
AGAINST MISMATING**
734-202/008-000 TO 734-220/008-000

ITEM-NO. (ITEM-NO.)	734-206/008-000
Cross section1 (Cross section / mm ²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.81
P (NO. OF POLES)	6
Height (Height / mm)	13.4
Width (Width / mm)	25.06
Depth (Depth / mm)	18.6
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	6
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles x Pin Spacing) + 2,2 mm