


| | | NATURAL | |
|---|---|---|---|
| HOUSING CKT. SIZE | DIM."A" | ENG. NO. | EDP. NO. |
| 2,4 | .387 (9.83) | 30072-04 | 15-97-9041 |
| 6 | .553 (14.05) | 30072-6 | 15-97-9061 |
| 8 | .718 (18.24) | 30072-8 | 15-97-9081 |
| 10 | .883 (22.43) | 30072-10 | 15-97-9101 |
| 12 | 1.049 (26.65) | 30072-12 | 15-97-9121 |
| 14 | 1.214 (30.84) | 30072-14 | NOT TOOLED |
| 16 | 1.379 (35.03) | 30072-16 | 15-97-9161 |
| 18 | 1.742 (44.25) | 30072-18 | NOT TOOLED |
| 20 | 1.907 (48.44) | 30072-20 | NOT TOOLED |
| 22 | 2.072 (52.63) | 30072-22 | NOT TOOLED |
| 24 | 2.238 (56.85) | 30072-24 | NOT TOOLED |

LEGEND

30072 - * *

CKT. SIZE

COLOR:
"BLANK" = NATURAL

NOTES:

1. MATERIAL: NYLON 6/6, U.L. 94V-2, COLOR: NATURAL.
2. FINISH : N/A
3. SEE PRODUCT SPECIFICATION # PS-5556-003.
4. PACKAGING SPECIFICATION: PK-30072-001.
5. PART IS FOR USE WITH HOUSINGS #30067 AND #30068.
6. PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

UPDATE NOTES
EC NO: UCP2010-2424
DRWN: JAGUILAR 2010/03/22
CHKD: JBELL 2010/04/09
APPR: FSMITH 2010/04/09
DESCRIPTION
REV
J

QUALITY SYMBOLS
F/A=0
F/C=0
F/P=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

| | mm | INCH |
|---|---|---|
| 4 PLACES | ± --- | ± --- |
| 3 PLACES | ± --- | ± .010 |
| 2 PLACES | ± 0.25 | ± .014 |
| 1 PLACE | ± 0.36 | ± --- |
| ANGULAR ±1/2° | | |

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: IN/MM
SCALE: 10:1
DESIGN UNITS: METRIC
THIRD ANGLE PROJECTION

DRAWN BY: DMF DATE: 1989/10/23
CHECKED BY: TGP DATE: 1989/10/23
APPROVED BY: FSMITH DATE: 1989/10/23 2010/04/09

TITLE: TPA LOCK FOR MINI-FIT HSGS 30067 & 30068

MOLEX INCORPORATED

MATERIAL NO.: SEE CHART
DOCUMENT NO.: SD-30072-*
SHEET NO.: 1 OF 1
SIZE: B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION