



ISSUE 9; February 2012 - RoHS 2011/65/EU

Description

- Standard 5x3.2mm SMD crystal with 4 pads.
Ceramic package with a seam sealed metal lid, hermetically sealed.
Please see our CFPX-225 for a two pad alternative.

Frequency Range

- Frequency 8.0000 to 150.0Mhz
- Frequency Tolerance $\pm 10\text{ppm}$ to $\pm 50\text{ppm}$

General Specification

- Load Capacitance (CL) 10.0pF to 30.0pF or Series
- Drive Level 100 μ W max
- Ageing $\pm 5\text{ppm}$ max per year @ 25°C
- Shunt Capacitance (C0) 7pF max

Operating Temperature Ranges

- 10 to 60°C
- 20 to 70°C
- 40 to 85°C

Environmental Parameters


- Drop: 75cm drop (3 times) onto hard wooden board
- Storage Temperature Range: -55 to 125°C
- Vibration: MIL-STD-202F, Method 204D, Test Condition D:
20G (10Hz-2000Hz), 4hrs in 3 mutually perpendicular planes
(total 12hrs)

Ordering Information

- Example
10.0MHz CFPX-104
50/50/-40 to 85C/10 FUND
- Frequency*
Model*
Frequency Tolerance (@25°C)*
Frequency Stability (over operating temperature range)*
Operating Temperature Range*
Load Capacitance*
Overtone*

Packing Details

- Pack Style: **Bulk** Loose in bulk pack
Pack Size 100
- Pack Style: **Reel** Tape & reel in accordance with EIA-481-D
Pack Size 1,000
- Alternative packing options available

**Outline (mm)****Sales Office Contact Details:**

UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18
USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

**Electrical Specification - maximum limiting values**

Frequency Range	Frequency Tolerance	Stability		Temperature Range	ESR Max	Vibration Mode
		Min	Max			
8.0 to <10.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	150Ω	Fundamental
10.0 to <12.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	90Ω	Fundamental
12.0 to <15.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	70Ω	Fundamental
15.0 to <20.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	50Ω	Fundamental
20.0 to <30.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	40Ω	Fundamental
30.0 to <40.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	30Ω	Fundamental
40.0 to <80.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	100Ω	3RD Overtone
40.0 to <52.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	20Ω	Fundamental
80.0 to <150.0MHz	±10ppm to ±50ppm	±10ppm ±15ppm ±20ppm	±50ppm	-10 to 60°C -20 to 70°C -40 to 85°C	80Ω	3RD Overtone

This document was correct at the time of printing; please contact your local sales office for the latest version

Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18

USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.comWeb: www.iqdfrequencyproducts.com