


REV.	DATE	DESCRIPTION
NC	05/05/97	INITIAL RELEASE
A	01/11/07	UPDATE DRAWING FORMAT



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .429"
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .118"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	01/11/07										
6						CHECKED			TNC REVERSE POLARITY CRIMP JACK (FOR BELDEN 9913, 9914)									
5						ISSUED												
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1											
3	CONTACT PIN	BRASS	GOLD	1						PART NO.								
2	INSULATOR	TEFLON	NATURAL	1						122392RP								
1	BODY	BRASS	NICKEL	1														
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE		C:/122/122392RP.DWG		DWG. NO.		122392RP.DWG	REV.	A	SIZE	A	SCALE	NA