



2020

SabreLite™ Recoil™

Similar to the SabreLite™ 2010 LED Flashlight, but with a voltage regulated LED that extends peak brightness. Recoil LED Technology results in a true collimated beam that cuts through thick smoke, fog, and dust. It is powered by 3 C alkaline cells.

- 10,000 Hours of Lamp Life
- 50% Longer Battery Life
- Built Pelican tough
- Recoil LED Technology: As bright as a Xenon light with the battery life of an LED
- Unconditional Lifetime Guarantee of Excellence



DIMENSIONS

Length	8.75" (22.2 cm)
---------------	-----------------

MATERIALS

Body	ABS
O-Ring	Ethylene Propylene
Lens	Polycarbonate (PC)
Shroud	Xenoy
Clip	ABS
Contact Spring Retainer	Stainless Steel / Brass Nickel

COLORS

 Black	 High Visibility Yellow
---	--

LIGHT SPECS

Lamp Type	LED
------------------	-----

POWER

Battery Size	C
Battery Type	Alkaline
Battery Quantity	3
Volts	4.5v

WEIGHT

Weight With Batteries	14.7 oz (417 gr)
Weight Without Batteries	7.3 oz (207 gr)
Packaged Weight	8.7 oz (247 gr)

SWITCH

Switch Type	Twisting Lens Shroud
--------------------	----------------------

Light Modes

On / Off

CERTIFICATIONS

Class I, Division 1**Class I, Division 2****OTHER**

Minimum Pack






1

Military

yes

Package Code

B

FL1 STANDARD	HIGH
	75 LUMENS
	6h 30mins
	113m
	3211cd
	IPX7

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 08-15-20