Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF-DOMETOP Bar..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'BT1.5M-M69'**

Your search criteria matched only one product, shown below

BT1.5M-M69

- Flammability rating of UL94V -0 – indoor use
- Dome -top head features unique patented design with round, smooth edges
- Stainless steel locking barb provides consistent performance, reliability, and infinite adjustability through entire bundle range
- High strength and low thread force
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light -Heavy cross section ties have a straight tip)
- Complementary flame retardant mounts available

Part Number	BT1.5M-M69
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, Metal Barb, 6.3"L (160mm), Miniature, Flame Retardant Nylon, Ivory
Product Type	Cable Ties
Material	Flame Retardant Nylon 6.6
Color	Ivory
CSA Certified	Yes
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Length (In.)	6.3
Length (mm)	160
Width (In.)	0.095
Width (mm)	2.4
CE Compliant	Yes
Cross Section	Miniature
Head Height (In.)	0.156
Head Height (mm)	4.0
Head Width (In.)	0.182
Head Width (mm)	4.6
Locking Style	Locking
Material Flammability Rating	V-0
Max. Bundle Diameter (In.)	1.50
Max. Bundle Diameter (mm)	38
Max. Continuous Use Temperature	212°F (100°C)
Min. Bundle Diameter (In.)	0.06
Min. Bundle Diameter (mm)	1.5
Min. Loop Tensile Strength (Lbs.)	18
Min. Loop Tensile Strength (N)	80
Plenum-Rated	No
Pricing Description	Cable Tie, Metal Barb, 6.3"L (160mm), Miniature, Flame Retardant Nylon, Ivory
Thickness (In.)	0.046
Thickness (mm)	1.2
Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy