

181-00213



Article Number: 181-00213

Slotted Wall Wiring Duct, 2.5" X 3", Non-Adhesive, PVC, Gray, 30ft/Box

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	181-00213
Type	SL2.5X3
Color	Gray (GY)
Features and Benefits	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
Product Description	Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and "Ts".
Short Description	Slotted Wall Wiring Duct, 2.5" X 3", Non-Adhesive, PVC, Gray, 30ft/Box

Product Dimensions

Length L (Imperial)	6.0 ft
Length L (Metric)	1.83 m
Width W (Imperial)	2.5 "
Width W (Metric)	63.5 mm
Width W2 (Imperial)	2.5 "
Width W2 (Metric)	63.5 mm
Width W3 (Imperial)	0.4 "
Width W3 (Metric)	10.2 mm
Width W4 (imperial)	1.0 "
Width W4 (metric)	25.4 mm
Width W5 (imperial)	2.6 "
Width W5 (metric)	66.0 mm
Width W6 (imperial)	0.75 "
Width W6 (metric)	19.05 mm
Height H (Imperial)	3.07 "
Height H (Metric)	77.9 mm
Mounting Hole Centers (Imperial)	4.0 "

Logistics and Packaging

Quantity Per	box
Package Quantity	30.0 ft

Package Quantity (Metric)	9.1 m
Carton Quantity	120.0 ft

Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	self-extinguishing
Operating Temperature	+122°F (+50°C)
ROHS Compliant	Yes
Certification/Specification	UL CSA
UL Listed (US and Canada)	No
UL Recognized (US)	Yes
UL Recognized (US and Canada)	No