

Thin Wall Heat-Shrinkable Tubing

2:1 Shrink Ratio

CPO Series — Thin-Wall Tubing, Non-Lined

- Flame-retardant, cross-linked polyolefin
- Continuous operating temperature: -55° C to 135° C
- Shrink temperature of 120° C
- Meets UL 224, 125° C; CSA C22.2 No. 198.1, 125° C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a



Shrink-Kon®

CPO Series Thin-Wall Heat-Shrinkable Tubing

CAT. NO.*	MINIMUM EXPANDED I.D. (IN.)	MAXIMUM REDUCED I.D. (IN.)	NOM. RECOVERED WALL THICKNESS (IN.)	CODE CABLE SIZE
CP063-_-	.06	.03	.02	—
CP093-_-	.09	.05	.02	—
CP0125-_-	.13	.06	.02	#24 – #30 AWG
CP0187-_-	.18	.09	.02	#14 – #22 AWG
CP0250-_-	.25	.13	.03	#10 – #16 AWG
CP0375-_-	.38	.19	.03	#6 – #12 AWG
CP0500-_-	.50	.25	.03	#1 – #6 AWG
CP0750-_-	.75	.38	.03	4/0 – #2 AWG
CP01000-_-	1.00	.50	.04	350 – 2/0 MCM

*See catalog construction to complete.

UL Recognized File Number E137759 and CSA Certified. (NOTE: Clear material not UL Recognized).

When ordering standard package, order by package not feet.

Larger diameters available upon special request; consult Customer Service.

Order multiple for 4' sticks is 25 sticks.

Order multiple for reels is 1 reel.

CATALOG NUMBER CONSTRUCTION

SERIES	COLOR	LENGTH FT.	FINAL ORDER NO.
CP063	+ 0 + C =		CP063-0-C
Available Colors		Available Packaging	
0 = Black		A = 4'	
C = Clear		25 = 25' reel	
2 = Red		C = 100' reel	
4 = Yellow		B = Bulk reel	
5 = Green		(See p. J-12 for lengths)	
6 = Blue			
9 = White			
S = Green & Yellow Striped*			

*Contact customer service for bulk reel quantity.

Thin-Wall Heat-Shrinkable Tubing Kit



CAT. NO.	DESCRIPTION	STD. PKG.
HS-KIT	Assortment of six different sizes (from 3/16" to 1") of black thin-wall heat-shrinkable tubing pre-cut to 6" lengths. Exceptional value; also includes handy plastic storage case.	1
CHS-KIT	Assortment of six different sizes (from 3/16" to 1") of multi-colored thin-wall heat-shrinkable tubing pre-cut to 6" lengths. Exceptional value; also includes handy plastic storage case.	1

Order multiple is std. pkg.

Thin-Wall Heat-Shrinkable Tubing, 6" lengths

CAT. NO.	MINIMUM EXPANDED I.D. (IN.)	MAXIMUM REDUCED I.D. (IN.)	NOMINAL RECOVERED WALL THICKNESS (IN.)	STD. PKG. QTY.
CP063-0-6	.06	.03	.02	20
CP093-0-6	.09	.05	.02	20
CP0125-0-6	.13	.06	.02	20
CP0187-0-6	.19	.09	.02	20
CP0250-0-6	.25	.13	.03	20
CP0375-0-6	.38	.19	.03	20
CP0500-0-6	.50/	.25	.03	10
CP0750-0-6	.75/	.38	.03	10
CP01000-0-6	1.00	.50	.04	5

Order multiple is std. pkg.

Catalog numbers listed are Black color, other colors available upon request.

Contact customer service.