



Dual-Rated T&B Catalog Number:

ADR60-12D

78378661032

Active

Description:

Type ADR-ALCUL Single-Conductor, Two-Hole Mount for Conductor Range Max 600 kcmil, Min 2 Str.

Features

Easy Installation - no special tools required.

General

Style	ALCUL Single-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	600 kcmil
Conductor Range (AL or CU) Minimum	2 Str.

Dimension Information

Length (inches)	5 5/16
Width (inches)	1 1/2
Height (inches)	1 1/2
D (inches)	5/8
E (inches)	1/2
F (inches)	3/8
G (inches)	3 1/16

Packaging

T&B Order Multiple	3
T&B Inner Pack	3
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	56.87 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000390
--------------------	------------

Notes

NEMA spacing 1 3/4 inch centers.

Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).

Certifications

RoHS Compliance	No
-----------------	----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com