

Item # 711-0019 Model 711 Electromechanical Hour Meter



Model 711 Electromechanical Hour Meter

A rectangular style AC hour meter designed to complement existing meters in control panels. Available in 6 figures reset or 7 figures non-reset. The non-reset model incorporates a retaining clip to lock into panel, while the reset version has a metal bracket and screw.

Specifications

Model No.	711
Mounting	Panel (Mounting hardware included)
Reset	Push-button
Termination	19 inch (483mm) wire leads
Display	6 figures, 0.19 inch (5mm) high 9,999.99 hours, (reset version)
Display Height	0.19 Inch
Display Height	5 mm
No. of Digits	6
Records	9999.99 hours
Input Voltage	115 VAC 60 Hz $\pm$ 10%
Power	2 watts (nominal)
Operating Temperature	-4 to +158 °F
Operating Temperature	-20 to +70 °C
Weight	2 oz
Weight	57 gm
Panel Cutout	1.98 x 0.99 Inch
Panel Cutout	50.3 x 25.1 mm
Approvals	UL Recognized, CSA Certified, CE Compliant
Stock Availability	No



Description

A rectangular style AC hour meter designed to complement existing meters in control panels. Available in 6 figure reset or 7 figure non-reset. The non-reset model incorporates a retaining clip to lock into panel, while the reset version has a metal bracket and screw.

Features

- Large figures
- 6 or 7 digits
- UL Recognized, CSA Certified, CE Compliant

Options

- Reset or non-reset

Specifications

Figures: 6 figure (reset) or 7 figure (non-reset), 0.19" [5mm] high
9,999.99 hours. (reset version)
99,999.99 hours. (non-reset models)

Reset: Push-button, or non-reset

Voltages: 115VAC (+/- 10%), 50 or 60 Hz.

Power: 2 watts (nominal)

Mounting: Panel (mounting hardware included)

Termination: 19" [483mm] wire leads

Temp. Range: -4°F to +158°F [-20°C to +70°C]

Approvals: UL Recognized, CSA Certified, CE Compliant

Weight: 2 oz. [57g]


Options: Voltages

Models

Model	Description
711-0019	115VAC/60Hz, reset, 6 figure, 9,999.99 hrs., 19" [483mm] wire leads
711-0020	115VAC/60Hz, non-reset, 7 figure, 99,999.99 hrs., 19" [483mm] wire leads
711-0041	115VAC/50Hz, non-reset, 7 figure, 99,999.99 hrs., 19" [483mm] wire leads


Dimensions

Non-Reset



Panel cutout: 1.98" x 0.99" [50.3 x 25.1]


Reset



Panel cutout: 1.98" x 0.99" [50.3 x 25.1]

Applications

Medical equipment



Test equipment



Office equipment

