THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECR-12-013445	18OCT12	KH	PD





1. SUPPLIED IN LOOSE PIECE
2. FOREIGN PRODUCTION ONLY.
3. MATING TAB THK IS 0.81±0.025 [.032±.001].
4. WIRE SIZE 0.8-1.3mm2 [18-16] AWG.
5. INSULATION RANGE IS 3.05-3.68 [.120-.145] DIA.
6. SPECIAL PACKAGE QTY
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI







7 OBSOLETE	—	6 8-41729-1
	41274-1	2 41729-2
	41274	41729
	STRIP	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL: BRASS
FINISH: TIN

DWN JR RUTH 2/11/91
CHK MS FEHER 2/11/91
APVD C MEYERS 2/11/91
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME: RECEPTACLE, FASTON, 6.35 [.250] SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-41729	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV L