


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					TOOLS
	ENGLISH	METRIC	L ± .03 [0,51]	W ± .01 [0,25]	C ± .02 [0,38]	M ± .03 [0,51]	H ± .01 [0,25]	
PMV1-3FB	--	M3	.85 [21,6]	.23 [5,84]	.19 [4,83]	.71 [18,03]	.13 [3,30]	CT-100A *CT-160 *CT-260 *CT-400 CT-600-A (CT-500CH) CT-600-A (CT-550CH) CT-1550 CT-1551 CT-2500 (CT-2550CH)
PV18-6F	#6	M3,5	.86 [21,8]	.30 [7,6]	.21 [5,3]	.69 [17,5]	.15 [3,8]	
PV18-6FN	#6	M3,5	.85 [21,6]	.24 [6,1]	.21 [5,3]	.69 [17,5]	.15 [3,8]	
PV18-8F	#8	M4	.93 [23,6]	.32 [8,1]	.25 [6,4]	.73 [18,5]	.17 [4,3]	
PV18-10F	#10	--	.93 [23,6]	.35 [8,9]	.25 [6,4]	.75 [19,1]	.20 [5,1]	
PV18-10FN	#10	--	.93 [23,6]	.31 [7,9]	.25 [6,4]	.75 [19,1]	.20 [5,1]	
PMV1-5FB	--	M5	.93 [23,6]	.36 [9,14]	.24 [6,10]	.76 [19,30]	.20 [5,1]	

*PANDUIT APPROVED TOOL

NOTES:

- cULus LISTED FOR:
 - 22-16 AWG [0,5-1,5 mm²] SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE
(1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- MATERIAL:
 - STAMPING: .032" [0,8] THK COPPER, TIN PLATED
 - HOUSING: VINYL, RED
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- WIRE STRIP LENGTH: 5/16 ^{+1/32}₋₀ [7,9 ^{+0,8}₋₀]



TITLE		2 PC. VINYL INSULATED, #22-18 BARREL, FORKS	
ITEM REVISION NAME		CUSTOMER DRAWING	
N41194BA/09			
DATASET FILE NAME			
N41194BA-DC/09A		MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		SEE NOTES	
.X ± .XX ± 		.XXX ± ANGLES ± THIRD ANGLE PROJECTION	
DRAWN BY		DRAWING NUMBER:	
FES		A41194	
DATE		SHEET 1 OF 1	
-		A	
CHK		SIZE	
FS		N.T.S.	