Honeywell

SMALL PRECISION LIMIT SWITCH

CATALOGUE LISTING
914CE SERIES
CHART MTG-CE-183

DO NOT SCALE PRINT

914CE SERIES
CHART MTG-CE-183

REPLACES

M

DRAWING NUMBER MS-11877

ISSUE 2/3

RELEASE NUMBER

REVISIONS
2 21/7/98
CO-543
3 0027391
MST 29DEC06



'L' METRES	CHARACTERISTICS					REL NO	CHK BY	I S S	CATALOGUE LISTING
	DIFF. TRAVEL (MAX)	OPERATING FORCE (MAX)		RELEASE FORCE (MIN)					
		NEWTONS	GmF	NEWTONS	GmF				
7	0.1	22.5	2300	4.4	450	MS-11877		1	914CE2-21N36
11	0.1	22.5	2300	4.4	450	MS-11877		1	914CE2-33N37

NOTES:-

1. DIE CAST HOUSING FINISHED WITH GREY PAINT.
2. TEMPERATURE RANGE: 0°C TO +70°C (STANDARD).
3. GOLD PLATED BASIC SWITCH USED IN THIS CONSTRUCTION 'G'.
4. ADDITIONAL PROTECTION AGAINST CUTTING FLUIDS 'KV'.

ELECTRICAL RATING	CIRCUIT DIAGRAM	CABLE	DIMENSIONS IN MM
c UL us E41859 5A-250 VAC 1/10HP-125/250 VAC	RED, BLACK, WHITE, GREEN CONTACT ARRANGEMENT:- S.P.D.T.	4 X 18 A.W.G. SJTO (UL/CSA APPROVED)	TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.15

THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.

THIRD ANGLE PROJECTION

MODIFY ON CAD3D SYSTEM ONLY

SCALE :- 1/1

DRAWN	R AITKEN	8/93
CHECK		
DESIGN	R AITKEN	8/93
AUTHOR'N		