

 Select Your Country/Region [Search](#)
[Home](#)[Products](#)[Support](#)[Services](#)[Selectors](#)[How to Buy](#)

APC PROTECTNET 10BASE2

Standalone data-line surge suppression for network, telecommunication and PC system protection.

Includes: User Manual

Part Number : **P10B2**

 [Compare Models](#) [Email Technical Specifications](#) [Printer Friendly](#)

Additional Information

[Product Overview](#)[Product Distribution](#)

Technical Specifications

Input

Input Connections	--
-------------------	----

Features:

- Catastrophic Event Protection

Surge Protection and Filtering

Peak Current Normal Mode	6.50 kAmps
Peak Current Common Mode	0.25 kAmps
NM Surge Response Time (ns)	1 ns
Data Lines Protected (multi-line only)	Centered Shielded Conductor
Let Through Voltage Rating	< 8

Physical

Net Weight	0.18 lbs. (0.08 kg)
Maximum Height	3.40 inches (86 mm)
Maximum Width	1.40 inches (36 mm)
Maximum depth	1.40 inches (36 mm)

Shipping Weight	0.20 lbs. (0.09 kg)
Shipping Height	7.00 inches (178 mm)
Shipping Width	6.50 inches (165 mm)
Shipping Depth	1.70 inches (43 mm)
Master Carton Weight	7.90 lbs.
SCC Codes	10731304000416
Color	Beige
Units per Pallet	1000.00

Environmental

Operating Environment	-15 - 65 °C (5 - 149 °F)
Operating Relative Humidity	0 - 95%
Storage Temperature	-15 - 65 °C (5 - 149 °F)
Storage Relative Humidity	0 - 95%

Conformance

Regulatory Approvals	UL 497B
Standard Warranty	Lifetime

[Copyright](#) © American Power Conversion Corp., all rights reserved
[About APC](#)[Investors](#)[Job Seekers](#)[Press](#)[Feedback](#)[Contact](#)[Privacy Policy](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APC:](#)

[P10B2](#)